



## SANODURE® FAST BRONZE L

***Sanodure Fast Bronze L*** produces shades of pink gold, bronze and orange with excellent light fastness, even on thin anodic coatings. Combinations with *Sanodure Fast Gold L* enable duplication of the entire range of gold colors from brassy to copper-like tones.

Chemical description:	Azo dye (granular)
Light fastness:	7 – 8 (very good)
Weather fastness:	Very good
Heat fastness:	Moderate up to 400° F.

### **RECOMMENDED APPLICATION DETAILS:**

Concentration:	0.5 - 5.0 g/l
pH range:	5.5 - 6.5
Buffering:	Anodal® Dye Buffer Liquid
Temperature:	120° - 140° F.
Immersion time:	2 - 20 minutes

### **PREFERRED SEALING METHODS:**

Hot:	Anodal ASL or Anodal AS
Medium:	Anodal MS-1 New or Anodal MTS Plus
Cold:	Anodal CS-2, Anodal CS-2N or Anodal CS3

### **PRECAUTIONS:**

This dye solution is affected by contamination with aluminum and other metal salts, including sulfates. Effective rinsing is advised.

### **ENVIRONMENTAL CONSIDERATIONS:**

This RoHS compliant product contains copper as an integral part of the dye. The preferred method of disposal is described in the Reliant bulletin, the *Anodal WT System*.

Recommendations, notices or instructions as to handling, use, storage or disposal of this product, including its use alone or in combination with other products, or as to any apparatus or process for its use are based upon information believed to be reliable. No liability is taken with respect to any such recommendations or instructions. Sole and exclusive warranty is that products comply with published chemical and physical specifications as provided on the certificate of analysis. No other warranties, either express or implied are given.